

nVent CADDY Macrofix Insulated Ventilation Duct Clamp



CERTIFICATIONS



CARACTERISTICI

Complete hanger assembly comes out of the box ready to install (sizes up to 600 mm)

Increased opening angle easily accommodates all standard-sized spiral ducts (sizes up to 600 mm)

Quick locking system prevents the hanger from accidentally opening when duct is moved or adjusted (sizes up to 600 mm)

Quick locking system easily closes with one hand (sizes up to 600 mm)

Thread impression retains quick locking captive screw and prevents it from falling out during installation

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICAȚII

Finish: Electrogalvanized

Temperature: -50 to 110 °C

Table 1/2

Număr de catalog	Article Number	Material	Outer Diameter (OD)	Rod Size (RS)	Width (W)	Thickness (T)
MFVI0080EG	586601	EPDM-SBR Rubber, Oțel	80 mm	M8, M10	20 mm	1 mm
MFVI0100EG	586603	EPDM-SBR Rubber, Oțel	100 mm	M8, M10	20 mm	1 mm
MFVI0125EG	586605	EPDM-SBR Rubber, Oțel	125 mm	M8, M10	20 mm	1 mm
MFVI0140EG	586606	EPDM-SBR Rubber, Oțel	140 mm	M8, M10	20 mm	1 mm
MFVI0150EG	586607	EPDM-SBR Rubber, Oțel	150 mm	M8, M10	20 mm	1 mm
MFVI0160EG	586608	EPDM-SBR Rubber, Oțel	160 mm	M8, M10	20 mm	1 mm
MFVI0200EG	586610	EPDM-SBR Rubber, Oțel	200 mm	M8, M10	20 mm	1 mm
MFVI0250EG	586612	EPDM-SBR Rubber, Oțel	250 mm	M8, M10	21 mm	1.25 mm
MFVI0300EG	586614	EPDM-SBR Rubber, Oțel	300 mm	M8, M10	21 mm	1.25 mm
MFVI0315EG	586615	EPDM-SBR Rubber, Oțel	315 mm	M8, M10	21 mm	1.25 mm
MFVI0355EG	586616	EPDM-SBR Rubber, Oțel	355 mm	M8, M10	21 mm	1.25 mm
MFVI0400EG	586617	EPDM-SBR Rubber, Oțel	400 mm	M8, M10	21 mm	1.25 mm
MFVI0450EG	586618	EPDM-SBR Rubber, Oțel	450 mm	M8, M10	21 mm	1.5 mm
MFVI0500EG	586619	EPDM-SBR Rubber, Oțel	500 mm	M8, M10	21 mm	1.5 mm
MFVI0560EG	586620	EPDM-SBR Rubber, Oțel	560 mm	M8, M10	21 mm	1.5 mm
MFVI0600EG	586621	EPDM-SBR Rubber, Oțel	600 mm	M8, M10	21 mm	1.5 mm




Număr de catalog	Article Number	Material	Outer Diameter (OD)	Rod Size (RS)	Width (W)	Thickness (T)
MFVI0630EG	586622	EPDM-SBR Rubber, Oțel	630 mm	M8, M10	23 mm	1.75 mm
MFVI0710EG	586623	EPDM-SBR Rubber, Oțel	710 mm	M8, M10	23 mm	1.75 mm
MFVI0800EG	586624	EPDM-SBR Rubber, Oțel	800 mm	M8, M10	23 mm	1.75 mm
MFVI0900EG	586625	EPDM-SBR Rubber, Oțel	900 mm	M8, M10	23 mm	1.75 mm

Table 2/2

Număr de catalog	Article Number	Screw Diameter (Sc)	Screw Length (L)	Angle (a)	Static Load
MFVI0080EG	586601	6	27mm	80 °	775N
MFVI0100EG	586603	6	27mm	80 °	775N
MFVI0125EG	586605	6	27mm	80 °	775N
MFVI0140EG	586606	6	40mm	80 °	775N
MFVI0150EG	586607	6	40mm	80 °	775N
MFVI0160EG	586608	6	40mm	80 °	775N
MFVI0200EG	586610	6	40mm	80 °	775N
MFVI0250EG	586612	6	40mm	80 °	1000N
MFVI0300EG	586614	6	40mm	80 °	1000N
MFVI0315EG	586615	6	40mm	80 °	1000N
MFVI0355EG	586616	6	40mm	80 °	1000N
MFVI0400EG	586617	6	40mm	80 °	1000N

Număr de catalog	Article Number	Screw Diameter (Sc)	Screw Length (L)	Angle (a)	Static Load
MFVI0450EG	586618	6	40mm	80 °	1400N
MFVI0500EG	586619	6	40mm	80 °	1400N
MFVI0560EG	586620	6	40mm	80 °	1400N
MFVI0600EG	586621	6	40mm	80 °	1400N
MFVI0630EG	586622	6	40mm		1900N
MFVI0710EG	586623	6	40mm		1900N
MFVI0800EG	586624	6	40mm		1900N
MFVI0900EG	586625	6	40mm		1900N

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

