

nVent CADDY Macrofix Plus Insulated



CERTIFICATIONS



CARACTERISTICI

Increased opening angle easily accommodates all standard-sized pipes

Quick locking system prevents the hanger from accidentally opening when pipe is moved or adjusted

Quick locking system easily closes with one hand

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Thread impression retains quick locking captive screw and prevents it from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICAȚII

Color: Black

Finish: Electrogalvanized

Temperature: -50 to 110 °C

Table 1/2

Număr de catalog	Article Number	Material	Outer Diameter (OD)	Rod Size (RS)	NB/DN	Width (W)
MFP015	586701	Oțel, EPDM-SBR Rubber	11 - 15 mm	M8, M10	8	20 mm
MFP019	586702	Oțel, EPDM-SBR Rubber	15 - 19 mm	M8, M10	10	20 mm
MFP025	586703	Oțel, EPDM-SBR Rubber	19 - 25 mm	M8, M10	15	20 mm
MFP031	586704	Oțel, EPDM-SBR Rubber	25 - 31 mm	M8, M10	20	20 mm
MFP037	586705	Oțel, EPDM-SBR Rubber	31 - 37 mm	M8, M10	25	20 mm
MFP044	586706	Oțel, EPDM-SBR Rubber	37 - 44 mm	M8, M10	32	20 mm
MFP051	586707	Oțel, EPDM-SBR Rubber	45 - 51 mm	M8, M10	40	21 mm
MFP058	586708	Oțel, EPDM-SBR Rubber	50 - 58 mm	M8, M10		21 mm
MFP068	586709	Oțel, EPDM-SBR Rubber	58 - 68 mm	M8, M10	50	21 mm
MFP078	586710	Oțel, EPDM-SBR Rubber	68 - 78 mm	M8, M10	65	23 mm
MFP088	586711	Oțel, EPDM-SBR Rubber	78 - 88 mm	M8, M10		23 mm
MFP098	586712	Oțel, EPDM-SBR Rubber	88 - 98 mm	M8, M10	80	23 mm
MFP108	586713	Oțel, EPDM-SBR Rubber	98 - 108 mm	M8, M10	90	23 mm
MFP118	586714	Oțel, EPDM-SBR Rubber	108 - 118 mm	M8, M10	100	23 mm
MFP128	586715	Oțel, EPDM-SBR Rubber	118 - 128 mm	M8, M10		23 mm
MFP138	586716	Oțel, EPDM-SBR Rubber	128 - 138 mm	M8, M10		23 mm
MFP148	586717	Oțel, EPDM-SBR Rubber	138 - 148 mm	M8, M10	125	25 mm

Număr de catalog	Article Number	Material	Outer Diameter (OD)	Rod Size (RS)	NB/DN	Width (W)
MFP160	586718	Oțel, EPDM-SBR Rubber	150 - 160 mm	M8, M10		25 mm
MFP170	586719	Oțel, EPDM-SBR Rubber	160 - 170 mm	M8, M10	150	25 mm
MFP200	586720	Oțel, EPDM-SBR Rubber	190 - 200 mm	M8, M10		27 mm
MFP215	586721	Oțel, EPDM-SBR Rubber	205 - 215 mm	M8, M10		27 mm

Table 2/2


Număr de catalog	Article Number	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load
MFP015	586701	1 mm	6	27mm	1000N
MFP019	586702	1 mm	6	27mm	1000N
MFP025	586703	1 mm	6	32mm	1000N
MFP031	586704	1 mm	6	32mm	1000N
MFP037	586705	1 mm	6	32mm	1000N
MFP044	586706	1 mm	6	37mm	1000N
MFP051	586707	1.25 mm	6	37mm	1500N
MFP058	586708	1.25 mm	6	37mm	1500N
MFP068	586709	1.25 mm	6	40mm	1500N
MFP078	586710	1.5 mm	6	40mm	2000N
MFP088	586711	1.5 mm	6	40mm	2000N
MFP098	586712	1.75 mm	6	45mm	2500N

Număr de catalog	Article Number	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load
MFP108	586713	1.75 mm	6	45mm	2500N
MFP118	586714	1.75 mm	6	50mm	2500N
MFP128	586715	2 mm	6	50mm	3000N
MFP138	586716	2 mm	6	50mm	3000N
MFP148	586717	2 mm	6	50mm	3200N
MFP160	586718	2 mm	6	50mm	3200N
MFP170	586719	2 mm	6	50mm	3200N
MFP200	586720	2.25 mm	6	50mm	3600N
MFP215	586721	2.25 mm	6	50mm	3600N

DETALII SUPLIMENTARE DESPRE PRODUS

Lining is EPDM rubber.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

