

nVent CADDY Speed Link Light Pack Spool Kit



The nVent CADDY Speed Link Light Pack Spool Kit includes a 150-meter long spool of 1mm wire rope together with 100 ultra-low-profile locking devices. The smart packaging allows contractors to pull and cut the wire length needed without having to take the spool out of the box, making it an ideal solution for every electrician to have on hand. The locking device has an aesthetic polished finish and a 10-kilogram load rating, ideal for supporting and securing lighting and signage.

CARACTERISTICI

Kit includes spool of nVent CADDY Speed Link steel wire and nVent CADDY Speed Link CLP locking devices

Wire spool and locking devices are packaged together, simplifying transportation to the jobsite and reducing inventory

Packaging allows end-users to pull and cut any length of wire that is needed without having to take the spool out of the box

Ideal for rework and installations where custom lengths of wire may be needed

Wire rope constructed from seven bundles of seven strands each of steel aircraft wire

Keyless release allows easy adjustments

Low-profile locking device minimizes visual impact

Keyless release tubes are easy to operate while wearing gloves

Double-sided locking mechanism enables simple height adjustment

SPECIFICAȚII

Table 1/1						
Număr de catalog	Article Number	Finish	Material	Wire Rope Diameter	Length	Number of Locking Devices
CLP1L500PACK	196095	Electrogalvaniz ed	Oțel, Brass	1 mm	150m	100

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare gresită sau orice altă lipsă de respectare completă a instrucțiunilor si

avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE



nVent.com/CADDY 2

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.