

nVent CADDY Speed Link SLK with Loop



CERTIFICATIONS



CARACTERISTICI

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

SPECIFICAȚII

Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Complies With:	SMACNA HVAC-DCS

Table 1/2

Număr de catalog	Article Number	Material	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)
------------------	----------------	----------	--------------------	------------------	------------	------------

SLK15L1LP	196601	Steel, Polypropylene, Zinc Alloy	1.5 mm	1m	101.6mm	55 mm
SLK15L1LPR2	196628	Steel, Polypropylene, Zinc Alloy	1.5 mm	1m	101.6mm	55 mm
SLK15L2LP	196514	Steel, Polypropylene, Zinc Alloy	1.5 mm	2m	101.6mm	55 mm
SLK15L2LPR2	196629	Steel, Polypropylene, Zinc Alloy	1.5 mm	2m	101.6mm	55 mm
SLK15L3LP	196515	Steel, Polypropylene, Zinc Alloy	1.5 mm	3m	101.6mm	55 mm
SLK15L3LPR2	196630	Steel, Polypropylene, Zinc Alloy	1.5 mm	3m	101.6mm	55 mm
SLK15L5LP	196516	Steel, Polypropylene, Zinc Alloy	1.5 mm	5m	101.6mm	55 mm
SLK15L7LP	196602	Steel, Polypropylene, Zinc Alloy	1.5 mm	7m	101.6mm	55 mm
SLK2L10LP	196606	Steel, Polypropylene, Zinc Alloy	2 mm	10m	101.6mm	55 mm
SLK2L1LP	196604	Steel, Polypropylene, Zinc Alloy	2 mm	1m	101.6mm	55 mm
SLK2L2LP	196543	Steel, Polypropylene, Zinc Alloy	2 mm	2m	101.6mm	55 mm
SLK2L3LP	196544	Steel, Polypropylene, Zinc Alloy	2 mm	3m	101.6mm	55 mm
SLK2L5LP	196545	Steel, Polypropylene, Zinc Alloy	2 mm	5m	101.6mm	55 mm
SLK3L10LP	196711	Steel, Polypropylene, Zinc Alloy	3 mm	10m	101.6mm	62 mm
SLK3L2LP	196707	Steel, Polypropylene, Zinc Alloy	3 mm	2m	101.6mm	62 mm


SLK3L3LP	196708	Steel, Polypropylene, Zinc Alloy	3 mm	3m	101.6mm	62 mm
SLK3L5LP	196709	Steel, Polypropylene, Zinc Alloy	3 mm	5m	101.6mm	62 mm

Table 2/2

Număr de catalog	Article Number	Width (W)	Thickness (T)	Angle (a)	Static Load	Certifications
SLK15L1LP	196601	19 mm	12.5 mm	90 ° Max	195N	UL, SMACNA, cUL
SLK15L1LPR2	196628	19 mm	12.5 mm	90 ° Max	195N	cUL, UL, SMACNA
SLK15L2LP	196514	19 mm	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK15L2LPR2	196629	19 mm	12.5 mm	90 ° Max	195N	SMACNA, UL, cUL
SLK15L3LP	196515	19 mm	12.5 mm	90 ° Max	195N	cUL, UL, SMACNA
SLK15L3LPR2	196630	19 mm	12.5 mm	90 ° Max	195N	SMACNA, cUL, UL
SLK15L5LP	196516	19 mm	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK15L7LP	196602	19 mm	12.5 mm	90 ° Max	195N	UL, SMACNA, cUL
SLK2L10LP	196606	19 mm	12.5 mm	90 ° Max	440N	UL, SMACNA, cUL
SLK2L1LP	196604	19 mm	12.5 mm	90 ° Max	440N	cUL, SMACNA, UL
SLK2L2LP	196543	19 mm	12.5 mm	90 ° Max	440N	cUL, UL, SMACNA
SLK2L3LP	196544	19 mm	12.5 mm	90 ° Max	440N	UL, cUL, SMACNA
SLK2L5LP	196545	19 mm	12.5 mm	90 ° Max	440N	UL, cUL, SMACNA
SLK3L10LP	196711	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L2LP	196707	24 mm	16 mm	90 ° Max	890N	SMACNA

Număr de catalog	Article Number	Width (W)	Thickness (T)	Angle (a)	Static Load	Certifications
SLK3L3LP	196708	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L5LP	196709	24 mm	16 mm	90 ° Max	890N	SMACNA

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

