

# Snap Close Conduit/Pipe Clamp



The nVent CADDY Snap Close Conduit Clamps (M-Series) are a fast and efficient method to secure conduit branch circuits for electrical installations. The M-Series is designed to provide positional consistency in application by eliminating conduit offset as well as maintain spacing entering electrical boxes. Increase installation efficiency by utilizing our comprehensive conduit range for your next electrical project.

## CERTIFICATIONS



## CARACTERISTICI

May be used for either vertical or horizontal installations

Eliminates need for offset bending conduit

Finger closure, no tools required

Locking design has greater resistance to twisting loads and is stronger than any on the market

Low profile locking tabs and smooth gripping dimples remove the possibility of scrapes

812M and 16M feature double tabs to center conduit, increase range and holding power and prevent conduit from sliding

## SPECIFICAȚII

Table 1/2

| Număr de catalog | Article Number | Material                        | Finish             | Outer Diameter (OD) | Hole Size (HS) | Hole Type |
|------------------|----------------|---------------------------------|--------------------|---------------------|----------------|-----------|
| 12MS1            | 179910         | Stainless Steel 301 (EN 1.4310) |                    | 22 - 30 mm          | 7 mm           | Plain     |
| 16M              | 170100         | Spring Steel                    | nVent CADDY Armour | 23.4 - 35 mm        | 7 mm           | Plain     |

| Număr de catalog | Article Number | Material                        | Finish             | Outer Diameter (OD) | Hole Size (HS) | Hole Type |
|------------------|----------------|---------------------------------|--------------------|---------------------|----------------|-----------|
| 20M              | 170110         | Spring Steel                    | nVent CADDY Armour | 35 - 42 mm          | 7 mm           | Plain     |
| 24M              | 170120         | Spring Steel                    | nVent CADDY Armour | 42 - 50 mm          | 7 mm           | Plain     |
| 32M              | 170130         | Spring Steel                    | nVent CADDY Armour | 50 - 60 mm          | 7 mm           | Plain     |
| 6M               | 170790         | Spring Steel                    | nVent CADDY Armour | 14 - 18 mm          | 7 mm           | Plain     |
| 812M             | 177130         | Spring Steel                    | nVent CADDY Armour | 18 - 30 mm          | 7 mm           | Plain     |
| 8MS1             | 179900         | Stainless Steel 301 (EN 1.4310) |                    | 18 - 22 mm          | 7 mm           | Plain     |

Table 2/2

| Număr de catalog | Article Number | Static Load 1 (F1) | Static Load 2 (F2) | Certifications |
|------------------|----------------|--------------------|--------------------|----------------|
| 12MS1            | 179910         | 440N               | 110N               |                |
| 16M              | 170100         | 440N               | 110N               | cUL, UL        |
| 20M              | 170110         | 440N               | 110N               | UL, cUL        |
| 24M              | 170120         | 440N               | 110N               | UL, cUL        |
| 32M              | 170130         | 440N               | 110N               | cUL, UL        |
| 6M               | 170790         | 440N               | 110N               | cUL, UL        |
| 812M             | 177130         | 440N               | 110N               | cUL, UL        |
| 8MS1             | 179900         | 440N               | 110N               |                |

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

