

Wire Spool



CARACTERISTICI

Spool with nVent CADDY Speed Link steel wire

Wire rope constructed from seven bundles of seven strands each of steel aircraft wire

SPECIFICAȚII

Finish: Electrogalvanized

Material: Oțel

Table 1/1

Număr de catalog	Article Number	Wire Rope Diameter	Length	Static Load
SLC15L1000SP	196001	1.5 mm	300m	195N
SLC15L50MSP	196023	1.5 mm	50m	195N
SLC2L100SP	196022	2 mm	100m	440N
SLC2L1000SP	196002	2 mm	300m	440N
SLC3L1000SP	196003	3 mm	300m	880N

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

