

# **Branch Line Restraint Pipe Attachment**

# **Data Solutions**



#### **CERTIFICATIONS**











#### CARACTERISTICI

Accepts 3/8" or 1/2" (M10 or M12) threaded rod

Quick grip clamp simplifies measuring and cutting of threaded rod

Eliminates need to cut threaded rod to exact dimensions

Works with rough-cut threaded rod and eliminates pipe-side deburring

Can be installed with threaded rod above or below the service pipe

Shear-off head helps ensure correct torque and simplifies inspection

#### **SPECIFICAȚII**

Finish: Electrogalvanized


Material: Oțel


Table 1/2						
Număr de catalog	Article Number	NB/DN	Outer Diameter (OD)	Rod Size (RS)	Height (H)	Length (L)

CSBBRP0200E G	404480	50	60.3mm	10, 12	100.3mm	68.3mm
CSBBRP0125E G	404478	32	42.2mm	10, 12	82.6mm	50mm
CSBBRP0150E G	404479	40	48.3mm	10, 12	88.9mm	56.1mm
CSBBRP0100E G	404477	25	33.4mm	10, 12	73.7mm	41.4mm

Table 2/2					
Număr de catalog	Article Number	Width (W)			
CSBBRP0200EG	404480	22.2mm			
CSBBRP0125EG	404478	22.2mm			
CSBBRP0150EG	404479	22.2mm			
CSBBRP0100EG	404477	22.2mm			

## **DIAGRAMS**





## **AVERTIZARE**

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE