

Cable to Web of Rail Mold Only, Signal

Data Solutions



CARACTERISTICI

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

SPECIFICAȚII

Rail Type: 85 lb to 141 lb T-Rail Sections

Material: Graphite

Table 1/1

Număr de catalog	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
SBB200CLH	1" Tab	3/16" Bondstrand	4.76mm	TB5, T21	Left Hand
SBB200CRH	1" Tab	3/16" Bondstrand	4.76mm	TB5, T21	Right Hand
SBW3150BLH	1" Tab	3/16" Bondstrand	4.76mm	TB5	Left Hand
SBW3150BRH	1" Tab	3/16" Bondstrand	4.76mm	TB5	Right Hand
SBB200YLH	1" Tab	16 mm ² Concentric	5.18mm	T21, TB5	Left Hand

Număr de catalog	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
SBB200YRH	1" Tab	16 mm ² Concentric	5.18mm	T21, TB5	Right Hand
SBB200XRH	1" Tab	25 mm ² Stranded	6.6mm	TB5, T21	Right Hand
SBB200PLH	1" Tab	35 mm ² Stranded	7.75mm	TB5, T21	Left Hand
SBB200PRH	1" Tab	35 mm ² Stranded	7.75mm	TB5, T21	Right Hand
SBWW6LH	Field-made	50 mm ² Solid	8mm	T21	Left Hand
SBWW6RH	Field-made	50 mm ² Solid	8mm	T21	Right Hand

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE