

Intelligent PDU, EN5xxx, 400 VAC, 3-PH

Data Solutions



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

CARACTERISTICI

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

SPECIFICAȚII

Table 1/6

Număr de catalog	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN5402	Enlogic	Intelligent PDU	Socket Strip	(18) C13, (6) C19	24	Black
EN5808	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (12) C19	24	Black
EN5810	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (12) C19	36	Black
EN5850	Enlogic	Intelligent PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black

Număr de catalog	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EN5812	Enlogic	Intelligent PDU	Socket Strip	(36) C13, (12) C19	48	Black

Table 2/6

Număr de catalog	Switched Outlets	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Input Cable Location	Input Voltage
EN5402	No	No Circuit Breaker	11.0 kVA	0	Top Feed	380 – 415V
EN5808	No	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5810	No	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5850	No	20 A, 1-pole, Hy-Mag	17.3 kVA North America, 22.1 kVA International	6	Top Feed	380 – 415V
EN5812	No	16 A, 1-pole, Hy-Mag		6	Top Feed	400V

Table 3/6

Număr de catalog	Phase	Interrupt Rating	Nominal Voltage	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)
EN5402	3 PH		415V	11.0 kVA	No	16 A
EN5808	3 PH		415V	22.0 kVA	No	32 A
EN5810	3 PH		415V	22.0 kVA	No	32 A
EN5850	3 PH		415V	17.3 / 22.1 kVA	No	30 A (24 A) North America, 32 A International
EN5812	3 PH WYE	5kAIC		22.0 kVA		32 A

Table 4/6

Număr de catalog	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material
------------------	----------------	------------	-----------	---------------	-----------------------	----------

EN5402	230VAC	0U	IEC 60309 516P6 (IP44)	Outlet	No	Oțel
EN5808	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	Yes	Oțel
EN5810	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	No	Oțel
EN5850	208 – 230VAC	0U	IEC 60309 530P6/532P6	Outlet	No	Oțel
EN5812	200 – 240VAC	0U	IEC 60309 532P6 (IP44)	Outlet	No	

Table 5/6

Număr de catalog	Finish	Height	Width	Depth	Weight	Package Quantity
EN5402	Vopsit Pulbere	1780mm	52mm	53mm	7.82kg	1
EN5808	Vopsit Pulbere	1780mm	52mm	53mm		1
EN5810	Vopsit Pulbere	1780mm	85mm	53mm	12.23kg	1
EN5850	Vopsit Pulbere	1780mm	56mm	75mm	11.93kg	1
EN5812						1

Table 6/6

Număr de catalog	Input Cable Length
EN5402	3m
EN5808	3m
EN5810	3m
EN5850	1.8m
EN5812	

DETALII SUPLIMENTARE DESPRE PRODUS

Please order bracket for vertical mounting separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE