

# nVent CADDY Cat HP J-Hook with T-Grid Clip

## Data Solutions



### CERTIFICATIONS



### CARACTERISTICI

No installation tools required for basic clip

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

### SPECIFICAȚII

Table 1/2

| Număr de catalog | Article Number | Material | Finish | Diameter (Ø) | Area | Cable Capacity, Cat 5e |
|------------------|----------------|----------|--------|--------------|------|------------------------|
|------------------|----------------|----------|--------|--------------|------|------------------------|

|           |        |                   |                                   |      |                    |    |
|-----------|--------|-------------------|-----------------------------------|------|--------------------|----|
| CAT16HPTS | 181089 | Oțel, Spring Oțel | nVent CADDY Armour, Pregalvanized | 25mm | 690mm <sup>2</sup> | 20 |
|-----------|--------|-------------------|-----------------------------------|------|--------------------|----|

Table 2/2

| Număr de catalog | Article Number | Cable Capacity, Cat 6 | Cable Capacity, Cat 6A | A    | Static Load |
|------------------|----------------|-----------------------|------------------------|------|-------------|
| CAT16HPTS        | 181089         | 15                    | 10                     | 65mm | 270N        |


## DETALII SUPLIMENTARE DESPRE PRODUS

Additional support wire required per NEC® 300.11.

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**