

# Varistar CP Steel Door, Perforated With 1-Point Locking

## Data Solutions



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

### CARACTERISTICI

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

### SPECIFICAȚII

**Product Type:** Cabinet Door

**Protection Rating:** IP20

**Material:** Oțel

Table 1/2

Număr de catalog	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-006	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-007	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-008	52U	2450mm	600mm	Single Point Locking	1	Black Grey

Număr de catalog	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-013	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-014	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-015	52U	2450mm	800mm	Single Point Locking	1	Black Grey
21630-408	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-409	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-410	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-411	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-412	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-413	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-414	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-415	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-507	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-508	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-509	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-510	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-511	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-512	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-513	38U	1800mm	600mm	Single Point Locking	1	Black Grey

Număr de catalog	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-514	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-515	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-516	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-517	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-518	47U	2200mm	800mm	Single Point Locking	1	Black Grey

Table 2/2				
Număr de catalog	Color Code	Complies With	Type	Works With
21630-006	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-007	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-008	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-013	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-014	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-015	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-408	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-409	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-410	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-411	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-412	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-413	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP

Număr de catalog	Color Code	Complies With	Type	Works With
21630-414	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-415	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-507	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-508	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-509	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-510	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-511	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-512	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-513	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-514	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-515	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-516	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-517	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-518	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP

## DETALII SUPLIMENTARE DESPRE PRODUS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**