

# Cable to Web of Rail T20 Complete Welder Pair, Power



## CARACTERISTICI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Each part number Includes both right and left hand welders

Includes mold cleaner and flint ignitor

## SPECIFICAȚII

**Bond Terminal Style:** W

Table 1/1

| Număr de catalog | Material                       | Rail Type                       | Conductor Size                | Conductor Outer Diameter, Nominal | Welder Style |
|------------------|--------------------------------|---------------------------------|-------------------------------|-----------------------------------|--------------|
| PBWT20Y301       | Graphite, Steel, Thermoplastic | UIC                             | 50 mm <sup>2</sup> Concentric | 8.9mm                             | T20          |
| PBWT20X3         | Graphite, Steel, Thermoplastic | UIC                             | 50 mm <sup>2</sup> Ropelay    | 9.13mm                            | T20          |
| PBWT202C         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 1/0 Concentric                | 9.47mm                            | T20          |
| PBWT202G         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 2/0 Concentric                | 10.62mm                           | T20          |
| PBWT202E         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 1/0 Ropelay                   | 10.87mm                           | T20          |

| Număr de catalog | Material                       | Rail Type                       | Conductor Size              | Conductor Outer Diameter, Nominal | Welder Style |
|------------------|--------------------------------|---------------------------------|-----------------------------|-----------------------------------|--------------|
| PBWT20X401       | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 70 mm <sup>2</sup> Ropelay  | 10.92mm                           | T20          |
| PBWT202J         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 2/0 Ropelay                 | 12.19mm                           | T20          |
| PBWT202Q         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 4/0 Concentric              | 13.41mm                           | T20          |
| PBWT20S6         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 14.5 mm Diameter            | 14.5mm                            | T20          |
| PBWT202S         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 4/0 Ropelay                 | 15.49mm                           | T20          |
| PBWT20X5         | Graphite, Steel, Thermoplastic | UIC                             | 95 mm <sup>2</sup> Ropelay  | 15.52mm                           | T20          |
| PBXLWT20X5       | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 95 mm <sup>2</sup> Ropelay  | 15.52mm                           | T20          |
| PBWT20X7         | Graphite, Steel, Thermoplastic | UIC                             | 150 mm <sup>2</sup> Ropelay | 17.04mm                           | T20          |
| PBWT203D         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 350 kcmil Concentric        | 17.3mm                            | T20          |
| PBWT20X8         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 185 mm <sup>2</sup> Ropelay | 17.8mm                            | T20          |
| PBWT202W         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 250 kcmil Ropelay           | 19.05mm                           | T20          |
| PBWT202W135      | Graphite, Steel, Thermoplastic | 135 lb Bethlehem                | 250 kcmil Ropelay           | 19.05mm                           | T20          |
| PBWT202W20AS     | Graphite, Steel, Thermoplastic | 20 lb ASCE                      | 250 kcmil Ropelay           | 19.05mm                           | T20          |
| PBWT20W40AS      | Graphite, Steel, Thermoplastic | 40 lb ASCE                      | 250 kcmil Ropelay           | 19.1mm                            | T20          |
| PBWT203B         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 300 kcmil Ropelay           | 20.32mm                           | T20          |
| PBWT203F         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 350 kcmil Ropelay           | 22.35mm                           | T20          |
| PBWT20X901       | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 240 mm <sup>2</sup> Ropelay | 23.62mm                           | T20          |
| PBWT203S         | Graphite, Steel, Thermoplastic | 85 lb to 141 lb T-Rail Sections | 500 kcmil Ropelay           | 26.42mm                           | T20          |

## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE