

# Cable to Web of Rail TB5 Complete Welder, Signal



## CARACTERISTICI

Complete right hand or left hand web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 141 lb. rail

## SPECIFICAȚII

**Bond Terminal Style:** 1" Tab

**Rail Type:** 85 lb to 141 lb T-Rail Sections

Table 1/1

| Număr de catalog | Material                       | Conductor Size   | Conductor Outer Diameter, Nominal | Welder Style | Orientation |
|------------------|--------------------------------|------------------|-----------------------------------|--------------|-------------|
| SBWRTB5ALH       | Graphite, Steel, Thermoplastic | 3/16" Bondstrand | 4.76mm                            | TB5          | Left Hand   |
| SBWRTB5ARH       | Graphite, Steel, Thermoplastic | 3/16" Bondstrand | 4.76mm                            | TB5          | Right Hand  |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**