

Cross Round Connector



CARACTERISTICI

Can be used for parallel or cross-run connections

SPECIFICAȚII

Table 1/2

Număr de catalog	Article Number	Material	Finish	Conductor Size	Depth (D)	Width (W)
CCR608S		Stainless Steel 18-8 (EN 1.4305)		6 mm Solid, 8 mm Solid, 8 mm Stranded	38.1mm	38.1 mm
CCR68CU	101260	Copper		6 mm Solid, 8 mm Solid, 8 mm Stranded	28mm	28 mm
CCR68GS	101265	Oțel	Hot-Dip Galvanized	6 mm Solid, 8 mm Solid, 8 mm Stranded	41mm	41 mm

Table 2/2

Număr de catalog	Article Number	Unit Weight
CCR608S		0.05 kg
CCR68CU	101260	0.05 kg
CCR68GS	101265	0.14 kg

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE