


Earthbridge DB, One Stud, Solid Round Steel, Straight



Earthbridges are assemblies made from a high-quality conductive earthpoint (connecting terminal) and various types of conductors. The nVent ERICO Cadweld exothermic connection process is used to combine them together, forming a highly corrosion resistant and long-lasting assembly.

DIAGRAMS



CARACTERISTICI

Long-lasting design

Low ground resistance and impedance

Superior electrical conductivity and resistance to corrosion

Electrically and mechanically robust and reliable

Easy to install

SPECIFICAȚII

Conductor Type: Solid Round Steel, Straight

Table 1/2

Număr de catalog	Material	Type	Earthpoint Type	Conductor Size	Length (L)	Diameter (Ø)
DB10KS12350	Copper, Oțel	DBKS	DB, One Stud	12 mm Diameter Solid	350mm	50 mm

Număr de catalog	Material	Type	EarthpointType	Conductor Size	Length (L)	Diameter (Ø)
DB10K16S050H	Copper, Oțel	DBKS	DB, One Stud	16 mm Diameter Solid	500mm	50 mm
DB10K16S050H G	Copper, Oțel	DBKS	DB, One Stud	16 mm Diameter Solid	500mm	50 mm
DB12K16S050H	Copper, Oțel	DBKS	DB, One Stud	16 mm Diameter Solid	500mm	50 mm
DB12K16S050H G	Copper, Oțel	DBKS	DB, One Stud	16 mm Diameter Solid	500mm	50 mm
DB16K16S050H	Copper, Oțel	DBKS	DB, One Stud	16 mm Diameter Solid	500mm	50 mm
BT12K16S050H G	Copper, Oțel	BTKS	B162, Two Stud	16 mm Diameter	500mm	

Table 2/2

Număr de catalog	Thread Size (TS)	Rebar Assembly Type	Hardware Included	Earthbridge Application	Complies With
DB10KS12350	M10	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA
DB10K16S050H	M10	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA
DB10K16S050HG	M10	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA
DB12K16S050H	M12	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA
DB12K16S050HG	M12	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA
DB16K16S050H	M16	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA
BT12K16S050HG	M12	Arc Welding to Rebar	Yes	Tunnel	EN IEC® 62561-1 Class H 100kA

DB-16-C-70-S-050-C		
DB	Earth Point	DB: 1 hole BT: 2 holes BF: 4 holes LU: M16 lug TA: tape
16	Thread Size	10: M10 12: M12 16: M16 40: Tape 40x5mm 30: Tape 30x4mm
C	Conductor Type	K: Steel Rond C: Y/G Cable T: Steel Bar F: Steel Bar 4mm N: NYY-O Cable H: N2XH-0 Cable
70	Conductor Size	12: D12mm 16: D16mm 30: 30x4mm 40: 40x5mm 50: 50mm ² 70: 70mm ² 95: 95mm ²
S	Conductor Angle	S: 0° P: 90° A: 45°
050	Length (cm)	xxx
x	Termination (option if cable)	SR: Solid Round EP: Earthpoint perpendicular ES: Earthpoint straight TA: Tape of 100mm TP: Tape of 150mm LU: M16 lug
x	Bolts & Washer	- : No Hardware H: With Hardware
C	Packaging	- : by unit (Made-to-Stock) C: 5 pieces (Made-to-Order) G: 25 pieces (Made-to-Order)

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

 **WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE