

ESE Air Terminal Remote Tester



The nVent ERICO Early Streamer Emission (ESE) Air Terminal Remote Tester is a fully autonomous monitoring system for Early Streamer Emission Air Terminals (ESEAT), requiring no additional costly hardware, software, monitoring or interface systems. Save time and money by avoiding equipment rentals required to manually test your ESE system. The nVent ERICO ESE Air Terminal Remote Tester features three LED lights to alert you if your ESEAT, tester, or complete system becomes inoperable at any time throughout the day. For easy monitoring, the LED lights are color-coded to indicate which part of the system needs replacement. The remote feature of the nVent ERICO ESE Air Terminal Remote Tester allows users to quickly ensure their lightning protection system is fully operational and their facility is protected at any time.

CARACTERISTICI

Allows for uninterrupted, daily monitoring of ESE system status

Fully autonomous

Requires no additional software or accessories

Colored LED lights indicate part-specific malfunctions to allow for quick and easy replacement

Easy installation and fast start-up time

Solar powered for sustainability (no batteries required)

Superior corrosion resistance, even in high salinity environments

Suitable for use with a variety of downconductor systems including tape and stranded conductors in addition to insulated downconductors such as nVent ERICO ISO_nV and nVent ERICO Ericore conductors

LED lights are visible up to 100 meters away

SPECIFICAȚII

Table 1/2

Număr de catalog	Material	Complies With	Enclosure Rating	Impulse Current (Iimp)	Status Indication	Working Temperature
SIREMOTETESTER	Stainless Steel 316L (EN 1.4404)	NF EN 62561-6 clause 6.6.4, EN 60529, EN 13032-1:2004, IEC@ 60068	IP 68	100kA 10/350 μs	LED	-20 to 60 °C

Table 2/2

Număr de catalog	Height	Length	Unit Weight	Width
SIREMOTETESTER	84 mm	185mm	1.25 kg	80 mm

DETALII SUPLIMENTARE DESPRE PRODUS

Compatible with SI60I316RT Early Streamer Emission Terminal (sold separately).

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE