

Ground Rod Clamp



CERTIFICATIONS



CARACTERISTICI

Unique stamped body design will not crack as mechanical forces are increased

Stainless steel threads will not strip if over-tightened

Unique internal profile offers pull-out load in excess of four times the UL® 96 requirement

Listed to UL® 96

SPECIFICAȚII

Table 1/2

Număr de catalog	Material	Conductor Size, UL	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Height (H)	Length (L)
LPC790	Copper	Class 1 - Class 2 (4/0 Max)	1/2" - 3/4"	12.7 - 17.3 mm	42 mm	44.5mm

Table 2/2

Număr de catalog	Width (W)	Unit Weight
LPC790	23.8 mm	0.15 kg

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE