

Joint Bond T7 Complete Welder Pair, Signal



CARACTERISTICI

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint

Connection is made within the confines of the splice bar

Includes mold cleaner and flint ignitor

SPECIFICAȚII

Rail Type: 85 lb to 141 lb T-Rail Sections

Table 1/1

Număr de catalog	Material	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style
SBHFT7E	Oțel, Graphite	Head Free	3/16" Bondstrand	4.76mm	T7
SBHFT7K	Oțel, Graphite	Head Free	5/16" Bondstrand	4.76mm	T7
SBTBT7F	Oțel, Graphite	3/4" Tab	3/16" Bondstrand	4.76mm	T7
SBTBT7G	Oțel, Graphite	1" Tab	3/16" Bondstrand	4.76mm	T7
SBXST7D	Oțel, Graphite	3/4" XS	3/16" Bondstrand	4.76mm	T7
SBTBT7B	Oțel, Graphite	1" Tab	5/16" Bondstrand	7.94mm	T7

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE