

Joint Bond T9 Mold Welder Frame Assembly, Power



CARACTERISTICI

Replacement welder frame assembly for T9 joint bond welders

Includes frame with mold lid, mold handle, mold cleaner and flint ignitor

SPECIFICAȚII

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: C

Table 1/1

Număr de catalog	Material	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBCT92JLHX	Graphite, Steel, Thermoplastic	2/0 Ropelay	12.19mm	T9	Left Hand Assembly
PBCT92JRHX	Graphite, Steel, Thermoplastic	2/0 Ropelay	12.19mm	T9	Right Hand Assembly
PBCT92SLHX	Graphite, Steel, Thermoplastic	4/0 Ropelay	15.49mm	T9	Left Hand Assembly
PBCT92SRHX	Graphite, Steel, Thermoplastic	4/0 Ropelay	15.49mm	T9	Right Hand Assembly
PBCT92WLHX	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T9	Left Hand Assembly

Număr de catalog	Material	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBCT92WRHX	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T9	Right Hand Assembly
PBCT92WX	Graphite, Steel, Thermoplastic	250 kcmil Ropelay	19.05mm	T9	Left and Right Hand Assembly

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE