

Prefabricated Cable Assembly



Safe 24 V operating low-voltage cable assembly is of simple design and rugged construction to ensure long life and minimum maintenance. The self-regulating feature enables the heating system to vary power output in response to changes in surrounding temperatures and weather conditions. As temperatures increase, the self-regulating cable automatically decreases its heat output, providing dependable over temperature protection. Self-regulating cables conserve energy by providing heat when and where it is needed over the entire circuit length. Available cable assemblies include 12 m (39.4') of regular electrical cable connected in our manufacturing facilities to self-regulating cable.

CARACTERISTICI

Self-regulating heating technology from nVent RAYCHEM

Touch-safe operating temperature

Prefabricated and tested in factory

Designed for installation into mounting channel

Rugged construction to withstand harsh environmental conditions

SPECIFICAȚII

Material: Copper;Fluoropolymer

Finish: Nickel Plated

Table 1/1

Număr de catalog	Length 1	Length 2	Operating Voltage	Temperature	Number of Conductors
RHS4TA9CA12	9 m	12 m	24 V	80 °C Max	2
RHS4TA6CA12	6 m	12 m	24 V	80 °C Max	2
RHS4TA7CA12	7 m	12 m	24 V	80 °C Max	2
RHS4TA4CA12	4 m	12 m	24 V	80 °C Max	2

DETALII SUPLIMENTARE DESPRE PRODUS

Length 1 represents the length of self-regulated heating cable. Length 2 represents the length of electrical cable.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE