

PVT1 Photovoltaic Surge Protection Class I+II



CERTIFICATIONS



CARACTERISTICI

Uniquely designed for protection of centralized solar inverters on the DC input side and string boxes

Thermal protection included to ensure safe failure modes

Compact, yet high surge rated pluggable design, using minimum DIN rail width

SPECIFICAȚII

Număr de catalog	PVT11000R	PVT11500R
Max Continuous Operating Voltage (Ucpv)	1100	1500
Nominal Discharge Current (In), IEC	20kA 8/20 μs	20kA 8/20 μs
Impulse Current (Iimp)	6.25kA 10/350 μs	5kA 10/350 μs
Total Discharge Current (Itotal)	12.5 50	10 40
Voltage Protection Level (Up)	4000V	5000V
Response Time	25 ns Max	25 ns Max
Short Circuit Current Rating (Isccr)	11kA	11kA

Număr de catalog	PVT11000R	PVT11500R
Max Continuous Operating Voltage (Vpdc)	1,100 VDC	1,500 VDC
Voltage Protection Rating (VPR)	2500V	4000V
Nominal Discharge Current (In), UL	20kA 8/20 μs	20kA 8/20 μs
Short Circuit Current Rating (SCCR)	50kA	65kA
Protection Modes	-ve to PE -ve to +ve +ve to PE	-ve to PE -ve to +ve +ve to PE
Altitude	2000 m Max	2000 m Max
Humidity	5 - 95	5 - 95
Temperature	-40 to 85 °C	-40 to 85 °C
Connection, Flexible	25 mm ²	25 mm ²
Connection, Solid	35 mm ²	35 mm ²
Connection, Stranded	35 mm ²	35 mm ²
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20	IP 20
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 125 VAC 1 A @ 250 VAC 0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC	1 A @ 125 VAC 1 A @ 250 VAC 0.5 A @ 12 VDC 0.5 A @ 24 VDC 0.5 A @ 48 VDC
Remote Contacts	Yes	Yes
Status Indication	Mechanical flag	Mechanical flag
Depth (D)	85mm	85mm
Height (H)	90 mm	90 mm
Width (W)	54 mm	54 mm
Unit Weight	0.46 kg	0.5 kg
Replacement Module	PVT1500M PVT1500SM	PVT1750M PVT1750SM
Certification Details	UL® 1449 Edition 4 Type 1CA	UL® 1449 Edition 4 Type 1CA
Complies With	EN IEC 61643-31, Type 1, Type 2	EN IEC 61643-31, Type 1, Type 2

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE