

SBHM Hollow Core Metal Tipped Rail Drill Bit



CARACTERISTICI

Designed for high-speed drilling applications

Withstands approximately 50 uses

Drill bits can be reground approximately five times

3/4" (19 mm) Weldon shank

Can be used on all rail types


Optional adaptor ADAPSBHM (716172) extends the length of the drill bit

SPECIFICAȚII

Table 1/1

Număr de catalog	Article Number	Material	Finish	Drill Bit Diameter (Ø)	Length (L)
SBHM2370	716322	High-Speed Steel	TIALN Coating	23 mm	63mm

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE