

# Special Track Work Complete Welder, Power



## CARACTERISTICI

Designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

## SPECIFICAȚII

**Rail Type:** Crane Rail Profiles

**Bond Terminal Style:** J

Table 1/1

Număr de catalog	Material	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation	Handle Length
PBJT503RH	Oțel, Graphite	2/0 Concentric	10.62mm	T5	Right Hand	502mm
PBJT503LH	Oțel, Graphite	2/0 Concentric	10.62mm	T5	Left Hand	502mm
PBJT52WRH	Graphite, Oțel	250 kcmil Ropelay	19.05mm	T5	Right Hand	502mm
PBJT52WLH	Oțel, Graphite	250 kcmil Ropelay	19.05mm	T5	Left Hand	502mm

## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE