

Stamped U-Bolt Pipe Clamp



CERTIFICATIONS



CARACTERISTICI

Clamp for bonding of pipes and exhaust stacks to the lightning protection system

Listed to UL® 96


SPECIFICAȚII

Material: Copper;Stainless Steel 304 (EN 1.4301)

Table 1/1

Număr de catalog	Outer Diameter (OD)	Depth (D)	Height (H)	Width (W)	Unit Weight	Certifications
LPC5966	111.1 - 174.2 mm	50.8mm	223.84 mm	211.15 mm	0.37 kg	
LPC5964	99.1 - 117.47 mm	50.8mm	147.64 mm	158.75 mm	0.4 kg	E202878-Combined_CoC, E202878-Combined_CoC

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE