

# Universal Conductor Clamp with Slide Rail



## CARACTERISTICI

Slides under tile and mechanically fastens to secure

Secures either round or tape conductors

## SPECIFICAȚII



Table 1/2

| Număr de catalog | Article Number | Material                                | Conductor Size           | Tape Size                       | Length (L) | Width (W) |
|------------------|----------------|-----------------------------------------|--------------------------|---------------------------------|------------|-----------|
| R6SFT40          | 104980         | Stainless Steel 18-8 (EN 1.4305), Nylon | 6 mm Solid - 11 mm Solid | 25 x 3 mm, 26 x 2 mm, 30 x 2 mm | 210mm      | 25 mm     |

Table 2/2

| Număr de catalog | Article Number | Hole Size (HS) | A         | Unit Weight |
|------------------|----------------|----------------|-----------|-------------|
| R6SFT40          | 104980         | 5 mm           | 18 mm Max | 0.08 kg     |

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE