

EB-130 Main Terminal Clamp



CERTIFICATIONS



CARACTERISTICI

For use with EB-130 or EB-2X130 Earthing and Neutral Busbars

Quick and easy installation

RoHS compliant

SPECIFICAȚII

Material: Brass

Finish: Nickel Plated



Table 1/2

Număr de catalog	Article Number	Conductor Size, IEC	Hole Size (HS)	Depth (D)	Height (H)	Width (W)
EB130CON70	568677	6 - 70 mm ² Stranded	5.5 mm	8mm	8 mm	31 mm
EB130CON35	568676	6 - 35 mm ² Stranded	5.5 mm	8mm	8 mm	22 mm

Table 2/2

Număr de catalog	Article Number	Torque (TQ)	Unit Weight
EB130CON70	568677	2 N·m	0.01 kg
EB130CON35	568676	2 N·m	0.01 kg

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE