

nVent ERIFLEX Flexbus IP55 Conductor Entry



nVent ERIFLEX Flexbus IP55 Conductor Entries can be used for switchboard and/or power supply cover to upgrade an installation to IP55 level. Protect the nVent ERIFLEX Flexbus Conductor insulation against sharp edges from power supply or switchboard top cover.

CERTIFICATIONS



CARACTERISTICI

Made with soft PVC to follow any potential conductor bending radius

Sealing around the conductor is made by a self-fusing tape with a strong adhesive

Good resistance to solvent and hydrocarbon splashes

Adaptable to any nVent ERIFLEX Flexbus conductor cross section by cutting the top material with traditional cutter

High acid resistance

UV resistance

RoHS compliant

Flame retardant

SPECIFICAȚII

Enclosure Rating:	IP 55
Material:	Polyvinylchloride
Working Temperature:	-40 to 140 °C

Table 1/2


Număr de catalog	Article Number	Type	A	B	C	Conductor Size
------------------	----------------	------	---	---	---	----------------

FLEXCEIP55C501	508140	Single Entry	126 mm	102 mm	175 mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²
FLEXCEIP55C1001	508141	Single Entry	176 mm	102 mm	152 mm	960 mm ² , 1280 mm ² , 1810 mm ²
FLEXCEIP55C502	508142	Double Entry	126 mm	157 mm	175 mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²
FLEXCEIP55C1002	508143	Double Entry	176 mm	157 mm	152 mm	960 mm ² , 1280 mm ² , 1810 mm ²

Table 2/2

Număr de catalog	Article Number	Torque (TQ)	Unit Weight
FLEXCEIP55C501	508140	2.5 N·m	0.6 kg
FLEXCEIP55C1001	508141	2.5 N·m	0.7 kg
FLEXCEIP55C502	508142	2.5 N·m	0.8 kg
FLEXCEIP55C1002	508143	2.5 N·m	1 kg

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE