

nVent ERIFLEX Zipflex Sleeve



CERTIFICATIONS



CARACTERISTICI

Quick and easy screening

Installation tool included

Halogen free

SPECIFICAȚII

Color:	Black
Material:	Polypropylene
Flammability Rating:	UL® 94HB
Working Temperature:	-30 to 140 °C

Table 1/1

Număr de catalog	Article Number	Diameter	Length	Unit Weight
ZFX100M8MMBK	554880	8 mm	100m	0.01 kg
ZFX50M15MMBK	554890	15 mm	50m	0.04 kg

Număr de catalog	Article Number	Diameter	Length	Unit Weight
ZFX30M20MMBK	554900	20 mm	30m	0.07 kg
ZFX20M25MMBK	554910	25 mm	20m	0.1 kg

DETALII SUPLIMENTARE DESPRE PRODUS

Unit weight is per meter (3.28').

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE