

Tinned Aluminum Earthing and Neutral Busbar



Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications such as switchgear and control equipment, electrical equipment, for wind and solar power generation and data centers.

CERTIFICATIONS



CARACTERISTICI

Tinned aluminum bar allows for copper or aluminum conductor connections

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Tin plating is corrosion resistant

Rigid bar

Can be fixed using IRS Angle Support Bracket, DMH Metallic Spacer or DH Distance Holder and Spacer

Quick and easy installation

RoHS compliant

SPECIFICAȚII

Material:	Aluminiu
Finish:	Tinned
Certification Details:	UL® 467

Număr de catalog	EB2AL	EB4AL	EB6AL	EB12AL	EB10AL	EB20AL

Article Number	568710	568711	568712	568714	568713	568715
Number of Connections	2	4	6	12	10	20
Hole Quantity	3	6	8	14	12	22
Conductor Size, IEC	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded	2.5 - 16 mm ² Stranded
Conductor Size, UL	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded	#14 - #4 Stranded
Max Current Rating	85A	85A	85A	85A	85A	85A
Height (H)	11.2 mm	11.2 mm	11.2 mm	11.2 mm	11.2 mm	11.2 mm
Width (W)	24.1 mm	47.8 mm	65 mm	112.5 mm	96.8 mm	176 mm
Depth (D)	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm	7.9mm
Unit Weight	0 kg	0.01 kg	0.02 kg	0.03 kg	0.03 kg	0.05 kg

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE