

CS480 Straight Coupling



CS480 Straight Coupling attaches a tube to the enclosure, enabling 340-degree enclosure rotation. Maintenance-free bearings.

STANDARDE INDUSTRIALE

IEC 60529, IP66

CARACTERISTICI

Coupling can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICAȚII

Table 1/1						
Număr de catalog	Height	Width	Depth	Material	Finish	Quick Ship
CCSS48FC	60mm	84mm	84mm	Stainless Steel 304	Lustruit	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE