

Ușă standard masivă | Dulapuri industriale, DN



Această ușă înlocuiește panoul spate al unui dulap industrial, pentru a permite accesul dinspre spate la echipamentele montate în partea din față sau pentru a monta contrapanourile spate în spate, în scopul de a crește spațiul disponibil pentru montaj.

CARACTERISTICI

Descriere: Ușă standard prevăzută cu sistem de închidere dublu-bit de 3 mm și cadru de ușă. Kit-ul de accesorii pentru ușă DNMK (balamale, tije de prindere) trebuie comandat separat. Permite toate opțiunile aferente programului de încuiere și balamalele cu deschidere la 180°. Compatibilă cu gama de dulapuri combinabilă și compactă.

Material: Placă din oțel de 2 mm.

Încărcare max.: 800 N.

Finisaj: Vopsea pudră structurată RAL 7035.

Cerințe montaj: Dacă anterior nu a fost montată o ușă este necesar kit-ul DNMK.

Cantitate pachet: 1 bucată.

SPECIFICAȚII

Color: Light Gray
Material: Oțel Zincat
Finish: Vopsit Pulbere
Color Code: RAL 7035

Table 1/1

Număr de catalog	Height	Width	Depth	Door Type	Enclosure Material	Product Family
DN2210R5	2182mm	993mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1106R5	1082mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1206LR5	1182mm	593mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1206R5	1182mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1206RR5	1182mm	593mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1208R5	1182mm	793mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1405LR5	1382mm	493mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1405RR5	1382mm	493mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1406LR5	1382mm	593mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1406R5	1382mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1406RR5	1382mm	793mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1408R5	1382mm	793mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1606LR5	1582mm	593mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1606R5	1582mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1606RR5	1582mm	593mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1608R5	1582mm	793mm	17mm	Plain	Oțel Zincat	Free-Standing

Număr de catalog	Height	Width	Depth	Door Type	EnclosureMaterial	Product Family
DN1610R5	1582mm	993mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1804LR5	1782mm	393mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1804RR5	1782mm	393mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1805LR5	1782mm	493mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1805R5	1782mm	493mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1805RR5	1782mm	493mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1806LR5	1782mm	593mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1806R5	1782mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1806RR5	1782mm	593mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1808LR5	1782mm	793mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN1808R5	1782mm	793mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1808RR5	1782mm	793mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN1810R5	1782mm	993mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2004LR5	1982mm	393mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN2004RR5	1982mm	393mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN2005LR5	1982mm	493mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN2005R5	1982mm	493mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2005RR5	1982mm	493mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN2006LR5	1982mm	593mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN2006R5	1982mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing

Număr de catalog	Height	Width	Depth	Door Type	EnclosureMaterial	Product Family
DN2006RR5	1982mm	593mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN2008LR5	1982mm	793mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN2008R5	1982mm	793mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2008RR5	1982mm	793mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN2010R5	1982mm	993mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2205LR5	2182mm	493mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN2205RR5	2182mm	493mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN2206LR5	2182mm	593mm	17mm	Left Door	Oțel Zincat	Free-Standing
DN2206R5	2182mm	593mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2206RR5	2182mm	593mm	17mm	Right Door	Oțel Zincat	Free-Standing
DN2208R5	2182mm	793mm	17mm	Plain	Oțel Zincat	Free-Standing
DN1804R5	1782mm	393mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2004R5	1982mm	393mm	17mm	Plain	Oțel Zincat	Free-Standing
DN2204R5	2182mm	393mm	17mm	Plain	Oțel Zincat	Free-Standing

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE