

ProLine Gland Plate



Adjustable Gland Plates are used to seal the bottom of the ProLine frame. Solid, vented and shielded Gland Plates are available. Solid and filtered gland plates include covers that are gasketed to maintain Type 12 enclosure requirements. All installation hardware is included. Solid Gland Plate and EMC Gland Plate are accessories to 100-mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed. EMC Gland Plate maintains a Type 1 rating.

CARACTERISTICI

Solid Gland Plate and EMC Gland Plate are accessories to 100- mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed.

Solid Gland Plate: the Solid Gland Plate can be used with all ProLine subpanels or rack angles. The gland plate consists of a base mounting surface and two adjustable foam-gasketed plates that permit cable entry. The plate can be rotated 180 degrees for front or rear cable entry.

EMC Gland Plate: This gland plate can be used with subpanels or rack angles. Gland plate consists of a base mounting surface and two adjustable gland plates (both have a conductive coating) with conductive fabric-over-foam gasket for cable entry.

Filtered (Vented) Gland Plate: Filtered Gland Plate is used only in conjunction with Vented Plinth Base Covers. The plate can be used with all ProLine subpanels or rack angles. It consists of a mounting base, three adjustable plates for cable entry, a filter and filter retaining rails. Manufactured from 16 gauge steel and finished with RAL 7035 textured light-gray polyester powder paint. Replacement filters available. EMC Gland Plate maintains a Type 1 rating.

All hardware included

SPECIFICAȚII

Thickness: 1.9mm
Color: Light Gray
Color Code: RAL 7035

Table 1/1

Număr de catalog	Material	Fits Frame Width	Fits Frame Depth	Finish	Quick Ship
PGP66	Oțel Zincat	600mm	600mm	Vopsit Pulbere	No
PGPV66	Oțel Zincat	600mm	600mm	Vopsit Pulbere	No
PGPV68	Oțel Zincat	600mm	800mm	Vopsit Pulbere	No
PGP68	Oțel Zincat	600mm	800mm	Vopsit Pulbere	No
PGPV85	Oțel Zincat	800mm	500mm	Vopsit Pulbere	No
PGP85	Oțel Zincat	800mm	500mm	Vopsit Pulbere	No
PGPV88	Oțel Zincat	800mm	800mm	Vopsit Pulbere	No
PGP88	Oțel Zincat	800mm	800mm	Vopsit Pulbere	No
PGPV64	Oțel Zincat	600mm	400mm	Vopsit Pulbere	No
PGP64	Oțel Zincat	600mm	400mm	Vopsit Pulbere	No
PGPV86	Oțel Zincat	800mm	600mm	Vopsit Pulbere	No
PGP86	Oțel Zincat	800mm	600mm	Vopsit Pulbere	No
PGP105	Oțel Zincat	1000mm	500mm	Vopsit Pulbere	No
PGPV106	Oțel Zincat	1000mm	600mm	Vopsit Pulbere	No
PGP106	Oțel Zincat	1000mm	600mm	Vopsit Pulbere	No
PGPV108	Oțel Zincat	1000mm	800mm	Vopsit Pulbere	No
PGP108	Oțel Zincat	1000mm	800mm	Vopsit Pulbere	No

Număr de catalog	Material	Fits Frame Width	Fits Frame Depth	Finish	Quick Ship
PGP84	Oțel Zincat	800mm	400mm	Vopsit Pulbere	No
PGPV65	Oțel Zincat	600mm	500mm	Vopsit Pulbere	No
PGP65	Oțel Zincat	600mm	500mm	Vopsit Pulbere	No
PGPV76	Oțel Zincat	700mm	600mm	Vopsit Pulbere	No
PGP78	Oțel Zincat	700mm	800mm	Vopsit Pulbere	No
PGPV78	Oțel Zincat	700mm	800mm	Vopsit Pulbere	No
PGPV89	Oțel Zincat	800mm	900mm	Vopsit Pulbere	No
PGP89	Oțel Zincat	800mm	900mm	Vopsit Pulbere	No
PGP79	Oțel Zincat	700mm	900mm	Vopsit Pulbere	No
PGP104	Oțel Zincat	1000mm	400mm	Vopsit Pulbere	No
PGP105AHF	Oțel Zincat	1000mm	500mm	Galvanizat	No
PGP108AHF	Oțel Zincat	1000mm	800mm	Galvanizat	No
PGP124	Oțel Zincat	1200mm	400mm	Vopsit Pulbere	No
PGP125	Oțel Zincat	1200mm	500mm	Vopsit Pulbere	No
PGP126	Oțel Zincat	1200mm	600mm	Vopsit Pulbere	No
PGP128	Oțel Zincat	1200mm	800mm	Vopsit Pulbere	No
PGP164	Oțel Zincat	1600mm	400mm	Vopsit Pulbere	No
PGP165	Oțel Zincat	1600mm	500mm	Vopsit Pulbere	No
PGP166	Oțel Zincat	1600mm	600mm	Vopsit Pulbere	No
PGP168	Oțel Zincat	1600mm	800mm	Vopsit Pulbere	No

Număr de catalog	Material	Fits Frame Width	Fits Frame Depth	Finish	Quick Ship
PGP185	Oțel Zincat	1800mm	500mm	Vopsit Pulbere	No
PGP186	Oțel Zincat	1800mm	600mm	Vopsit Pulbere	No
PGP188	Oțel Zincat	1800mm	800mm	Vopsit Pulbere	No
PGP45	Oțel Zincat	400mm	500mm	Vopsit Pulbere	No
PGP46	Oțel Zincat	400mm	600mm	Vopsit Pulbere	No
PGP64AHF	Oțel Zincat	600mm	400mm	Galvanizat	No
PGP65AHF	Oțel Zincat	600mm	500mm	Galvanizat	No
PGP66AHF	Oțel Zincat	600mm	600mm	Galvanizat	No
PGP68AHF	Oțel Zincat	600mm	800mm	Galvanizat	No
PGP78AHF	Oțel Zincat	700mm	800mm	Galvanizat	No
PGP79AHF	Oțel Zincat	700mm	900mm	Galvanizat	No
PGP88AHF	Oțel Zincat	800mm	800mm	Galvanizat	No
PGP89AHF	Oțel Zincat	800mm	900mm	Galvanizat	No
PGPV125	Oțel Zincat	1200mm	500mm	Vopsit Pulbere	No
PGPV126	Oțel Zincat	1200mm	600mm	Vopsit Pulbere	No
PGPV128	Oțel Zincat	1200mm	800mm	Vopsit Pulbere	No
PGPV165	Oțel Zincat	1600mm	500mm	Vopsit Pulbere	No
PGPV166	Oțel Zincat	1600mm	600mm	Vopsit Pulbere	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și

avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE