

Swing-Out Panel



Swing-Out Panels allow a front-mounted panel to pivot out of an enclosure frame opening. This accessory includes a panel and all the necessary hardware. Panels provide 170 degrees of rotation, with the capability to hinge from the right or left side.

CARACTERISTICI

Swing-Out Panels are available for 600-, 700- and 800-mm wide enclosures

Spring-loaded pivot post allows for easy installation

Hinge blocks are anodized black; supports and panel have a painted white finish

Quarter-turn latches are provided to secure the Swing-Out Panel in the closed position

Panels provide 170 degrees of rotation, with the capability to hinge from the right or left side.

All necessary mounting hardware included

SPECIFICAȚII

Thickness: 2.66mm
Finish: Vopsit Pulbere
Color: White

Table 1/1

Număr de catalog	Material	Fits Frame Width	Quick Ship
PSP146	Oțel Zincat	600mm	No
PSP148	Oțel Zincat	800mm	No
PSP166	Oțel Zincat	600mm	No
PSP168	Oțel Zincat	800mm	No
PSP186	Oțel Zincat	600mm	No
PSP188	Oțel Zincat	800mm	No
PSP206	Oțel Zincat	600mm	No
PSP208	Oțel Zincat	800mm	No
PSP226	Oțel Zincat	600mm	No
PSP228	Oțel Zincat	800mm	No
PSP76	Oțel Zincat	600mm	No
PSP78	Oțel Zincat	800mm	No
PSP147	Oțel Zincat	700mm	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE