

Telescope Fitting Feed-Through Stainless Steel



Feed-Through Stainless Steel Telescope Fittings are for adjusting wireway length without cutting or welding. Length is easily adjustable from 1.50 in. to 13.50 in. (343 mm). Connects to other wireway sections and fittings and protects wires and cables in frequently hosed down, very wet or highly corrosive applications.

CARACTERISTICI

Fitingurile telescopice de trecere din oțel inoxidabil sunt utilizate pentru ajustarea lungimii canalului de cablu fără tăiere sau sudură

Length is easily adjustable from 1.50 in. to 13.50 in. (343 mm)

Connects to other wireway sections and fittings and protects wires and cables in frequently hosed down, very wet or highly corrosive applications

SPECIFICAȚII

Finish: No. 2B
Material: Stainless Steel 304

Table 1/1					
Număr de catalog	Type	Height	Width	Thickness	Quick Ship
F66WASS	Telescope Fitting	152mm	152mm	1.59mm	No
F44WASS	Telescope Fitting	102mm	102mm	1.59mm	No

DETALII SUPLIMENTARE DESPRE PRODUS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE