

nVent LENTON Interlok HYA15HT Grout Additive, Hot Temperature



The nVent LENTON HYA15LM Grout Additive, Hot Temperature is designed to be used in conjunction with nVent LENTON Interlok grout-fill couplers and nVent LENTON Interlok HY15LM Grout. The additive is used to increase working time of the grout during hot temperature applications which allows for a longer time window to place the grout into the Interlok couplers. This proprietary grout additive increases the maximum working temperature of HY15LM grout from 100 °F (38 °C) to 122 °F (50 °C).

CARACTERISTICI

Allows for hot temperature grouting

Increases grout working time in hot climates

Extends the construction season

For use in pump or gravity fill applications

SPECIFICAȚII

Table 1/1

Număr de catalog	Compressive Strength	Working Temperature	Unit Weight
HYA15HT	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	21 to 50 °C	0.05 kg

DETALII SUPLIMENTARE DESPRE PRODUS

For use with HY15LM grout only.

Hot weather concreting procedures, such as ACI 305 Hot Weather Concreting, must be followed.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

HYA15HT can be used in temperatures as low as 70 °F (21 °C) to extend working time; however, this may slow the compressive strength curve.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE