


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

Power Utilities

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



CERTIFICATIONS



CARACTERISTICI

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

SPECIFICAȚII

Table 1/3

Număr de catalog	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-474	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-473	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-472	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-174	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-173	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-172	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile

Table 2/3

Număr de catalog	Shock and Vibration Tolerance	Handle Included	Mounting	Complies With	EMC Shielding	Product Type
24563-474	5 g (force)	No	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24563-473	5 g (force)	No	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24563-472	5 g (force)	No	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24563-174	5 g (force)	No	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24563-173	5 g (force)	No	Rack	IEC 60297-3-103	Yes	Subrack/Chassis
24563-172	5 g (force)	No	Rack	IEC 60297-3-103	Yes	Subrack/Chassis

Table 3/3

Număr de catalog	Rack Width	Static Load
24563-474	84 HP	15 kgf
24563-473	84 HP	15 kgf

Număr de catalog	Rack Width	Static Load
24563-472	84 HP	15 kgf
24563-174	84 HP	15 kgf
24563-173	84 HP	15 kgf
24563-172	84 HP	15 kgf

DETALII SUPLIMENTARE DESPRE PRODUS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE