

Novastar Cabinet With Glazed Door and Rear Panel

Power Utilities



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICATIONS



CARACTERISTICI

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

SPECIFICAȚII

Table 1/3

Număr de catalog	Rack Height	Frame Color	Height	Frame Color Code	Cladding Material	Width
------------------	-------------	-------------	--------	------------------	-------------------	-------

15230-019	12 U	Black Grey	589 mm	RAL 7021	Oțel	553 mm
16230-019	12 U	Black Grey	589 mm	RAL 7021	Oțel	553 mm
15230-020	16 U	Black Grey	767 mm	RAL 7021	Oțel	553 mm
16230-020	16 U	Black Grey	767 mm	RAL 7021	Oțel	553 mm
15230-021	20 U	Black Grey	945 mm	RAL 7021	Oțel	553 mm
16230-021	20 U	Black Grey	945 mm	RAL 7021	Oțel	553 mm
15230-022	38 U	Black Grey	1745 mm	RAL 7021	Oțel	553 mm
15230-023	38 U	Black Grey	1745 mm	RAL 7021	Oțel	553 mm
16230-022	38 U	Black Grey	1745 mm	RAL 7021	Oțel	553 mm
16230-023	38 U	Black Grey	1745 mm	RAL 7021	Oțel	553 mm
15230-024	43 U	Black Grey	1967 mm	RAL 7021	Oțel	553 mm
15230-025	43 U	Black Grey	1967 mm	RAL 7021	Oțel	553 mm
16230-024	43 U	Black Grey	1967 mm	RAL 7021	Oțel	553 mm
16230-025	43 U	Black Grey	1967 mm	RAL 7021	Oțel	553 mm

Table 2/3

Număr de catalog	Cladding Color	Depth	Static Load	Cladding Color Code	Complies With	Frame Material
15230-019	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu
16230-019	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu
15230-020	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu

Număr de catalog	Cladding Color	Depth	Static Load	Cladding Color Code	Complies With	Frame Material
16230-020	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu
15230-021	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu
16230-021	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu
15230-022	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu
15230-023	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu
16230-022	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu
16230-023	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu
15230-024	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu
15230-025	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminiu
16230-024	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu
16230-025	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminiu

Table 3/3

Număr de catalog	Product Type	Protection Rating
15230-019	Cabinet	IP20
16230-019	Cabinet	IP20
15230-020	Cabinet	IP20
16230-020	Cabinet	IP20
15230-021	Cabinet	IP20
16230-021	Cabinet	IP20

Număr de catalog	Product Type	Protection Rating
15230-022	Cabinet	IP20
15230-023	Cabinet	IP20
16230-022	Cabinet	IP20
16230-023	Cabinet	IP20
15230-024	Cabinet	IP20
15230-025	Cabinet	IP20
16230-024	Cabinet	IP20
16230-025	Cabinet	IP20

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE