

Varistar CP Bottom Rear Panel, Shortened

Power Utilities

Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

CARACTERISTICI

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPECIFICAȚII

Table 1/2

Număr de catalog	Rack Height	Height	Width	Protection Rating	Color	Color Code
21630-354	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-355	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-356	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-357	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-358	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021
21630-359	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021

Table 2/2

Număr de catalog	Product Type
21630-354	Cabinet Door

Număr de catalog	Product Type
21630-355	Cabinet Door
21630-356	Cabinet Door
21630-357	Cabinet Door
21630-358	Cabinet Door
21630-359	Cabinet Door

DETALII SUPLIMENTARE DESPRE PRODUS

The height of the rear panel is 400 mm less than the cabinet height to accomodate the connecting plate.

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE