

Varistar CP IP 20 Cabinet, Glass Front Door, Steel Rear Door

Power Utilities

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

CARACTERISTICI

Type of protection IP 20

With glass front door

Doors with single point locking, side panels with quick release fastener

Static load-carrying capacity 1600 kg

SPECIFICAȚII

Table 1/3

Număr de catalog	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-038	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Oțel
10630-037	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Oțel
10630-039	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Oțel
10630-040	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Oțel

Table 2/3

Număr de catalog	Depth	Cladding Color	Cladding Color Code	Complies With	Frame Material	Product Type
------------------	-------	----------------	---------------------	---------------	----------------	--------------

10630-038	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Oțel	Cabinet
10630-037	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Oțel	Cabinet
10630-039	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Oțel	Cabinet
10630-040	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Oțel	Cabinet

Table 3/3

Număr de catalog	Protection Rating	Static Load
10630-038	IP20	1600 kgf
10630-037	IP20	1600 kgf
10630-039	IP20	1600 kgf
10630-040	IP20	1600 kgf

DETALII SUPLIMENTARE DESPRE PRODUS

Lever handle can be added to the doors.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE