

Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking

Power Utilities

EMC and IP55 Steel Door with lever handle and 4-Point locking.

CARACTERISTICI

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

SPECIFICAȚII

Table 1/2

Număr de catalog	Rack Height	Height	Width	Color	Color Code	Complies With
21630-760	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-761	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-762	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-763	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-764	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Număr de catalog	Rack Height	Height	Width	Color	Color Code	Complies With
21630-765	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-766	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-767	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Table 2/2

Număr de catalog	Locking Type	Material	Product Type	Protection Rating	Type	Works With
21630-760	4-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-761	4-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-762	4-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-763	4-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-764	4-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-765	4-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-766	5-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-767	5-Point Locking	Oțel	Cabinet Door	IP55	Steel Door, Plain	Varistar CP

DETALII SUPLIMENTARE DESPRE PRODUS

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O

instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE