

19" Fan Unit, 1 U, Speed Control and Monitoring

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



CARACTERISTICI

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPECIFICAȚII

Table 1/2

Număr de catalog	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Certifications
10713-098		24V min	1	Aluminum-Zinc Plated, Anodized	Oțel, Aluminu	CE, RoHS, EAC
19713-121	230V		1	Aluminum-Zinc Plated, Anodized	Oțel, Aluminu	EAC, RoHS

Număr de catalog	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Certifications
19713-006	230V		1	Aluminum-Zinc Plated, Anodized	Oțel, Aluminu	CE, RoHS, EAC
10713-099		24V min	1	Aluminum-Zinc Plated, Anodized	Oțel, Aluminu	EAC, CE, RoHS

Table 2/2

Număr de catalog	Quick Ship
10713-098	No
19713-121	No
19713-006	No
10713-099	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE