

19" Mounting Bracket

Easy mounting for connection system for networks which are reliable, gas-tight connection between the contact and conductor.



CERTIFICATIONS



CARACTERISTICI

Mounting height 1 U

For the assembly of cable channels and system rails (Z.w.LSA+ or Infra+)

SPECIFICAȚII

Product Type: Bracket

Material: Oțel

Table 1/1

Număr de catalog	Depth	Package Quantity	Finish	Type	Works With	Quick Ship
30118-802	70mm	1	Vopsit Pulbere	Mounting Bracket	LSA+ Guide Rails	No
30118-803	170mm	1	Vopsit Pulbere	Mounting Bracket	LSA+ Guide Rails	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order 19" assembly kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE