

CompacPRO Desktop Case, Unshielded



The nVent SCHROFF CompacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frame and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



CARACTERISTICI

Desktop case for individual assembly

Aluminum construction ensures robust solution

International dimensions in accordance with IEC 6297-3-101

Side panel with integrated handle function

Front and rear identical, depth-symmetrical construction

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

SPECIFICAȚII

Product Type:	Case
Type:	Case for Individual Electronic Components
Product Family:	CompacPRO

Table 1/3

Număr de catalog	Rack Height	Height	Rack Width	Width	Depth	Package Quantity
------------------	-------------	--------	------------	-------	-------	------------------

14575-023	2U	102.6mm	42HP	257mm	271mm	1
14575-025	2U	102.6mm	42HP	257mm	331mm	1
14575-027	2U	102.6mm	42HP	257mm	391mm	1
14575-063	2U	102.6mm	84HP	471mm	271mm	1
14575-065	2U	102.6mm	84HP	471mm	331mm	1
14575-067	2U	102.6mm	84HP	471mm	391mm	1
14575-103	3U	147.1mm	28HP	186mm	271mm	1
14575-105	3U	147.1mm	28HP	186mm	331mm	1
14575-123	3U	147.1mm	42HP	257mm	271mm	1
14575-125	3U	147.1mm	42HP	257mm	331mm	1
14575-127	3U	147.1mm	42HP	257mm	391mm	1
14575-143	3U	147.1mm	63HP	364mm	271mm	1
14575-145	3U	147.1mm	63HP	364mm	331mm	1
14575-147	3U	147.1mm	63HP	364mm	391mm	1
14575-163	3U	147.1mm	84HP	471mm	271mm	1
14575-165	3U	147.1mm	84HP	471mm	331mm	1
14575-167	3U	147.1mm	84HP	471mm	391mm	1
14575-169	3U	147.1mm	84HP	471mm	451mm	1
14575-171	3U	147.1mm	84HP	471mm	511mm	1

14575-223	4U	191.6mm	42HP	257mm	271mm	1
14575-225	4U	191.6mm	42HP	257mm	331mm	1
14575-243	4U	191.6mm	63HP	364mm	271mm	1
14575-245	4U	191.6mm	63HP	364mm	331mm	1
14575-247	4U	191.6mm	63HP	364mm	391mm	1
14575-265	4U	191.6mm	84HP	471mm	331mm	1
14575-267	4U	191.6mm	84HP	471mm	391mm	1
14575-269	4U	191.6mm	84HP	471mm	451mm	1
14575-271	4U	191.6mm	84HP	471mm	511mm	1
14575-445	6U	280.5mm	63HP	364mm	331mm	1
14575-447	6U	280.5mm	63HP	364mm	391mm	1
14575-463	6U	280.5mm	84HP	471mm	271mm	1
14575-465	6U	280.5mm	84HP	471mm	331mm	1
14575-467	6U	280.5mm	84HP	471mm	391mm	1
14575-469	6U	280.5mm	84HP	471mm	451mm	1
14575-471	6U	280.5mm	84HP	471mm	511mm	1

Table 2/3

Număr de catalog	Usable Height	Usable Width	Front Frame Construction	Cooling Option	Complies With	EMC Shielding
14575-023	84.4mm	219mm	Single Piece	No	IEC 60297-3-103	No

Număr de catalog	Usable Height	Usable Width	Front Frame Construction	Cooling Option	Complies With	EMC Shielding
14575-025	84.4mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-027	84.4mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-063	84.4mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-065	84.4mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-067	84.4mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-103	129.3mm	148mm	Single Piece	No	IEC 60297-3-103	No
14575-105	129.3mm	148mm	Single Piece	No	IEC 60297-3-103	No
14575-123	129.3mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-125	129.3mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-127	129.3mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-143	129.3mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-145	129.3mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-147	129.3mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-163	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-165	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-167	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-169	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-171	129.3mm	432mm	Single Piece	No	IEC 60297-3-103	No

Număr de catalog	Usable Height	Usable Width	Front Frame Construction	Cooling Option	Complies With	EMC Shielding
14575-223	173.8mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-225	173.8mm	219mm	Single Piece	No	IEC 60297-3-103	No
14575-243	173.8mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-245	173.8mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-247	173.8mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-265	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-267	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-269	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-271	173.8mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-445	262.9mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-447	262.9mm	326mm	Single Piece	No	IEC 60297-3-103	No
14575-463	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-465	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-467	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-469	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No
14575-471	262.9mm	432mm	Single Piece	No	IEC 60297-3-103	No

Table 3/3

Număr de catalog	Finish	Material	Protection Rating	Static Load	Quick Ship
14575-023	Vopsit Pulbere	Aluminiu	IP20	30kg	No

Număr de catalog	Finish	Material	Protection Rating	Static Load	Quick Ship
14575-025	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-027	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-063	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-065	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-067	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-103	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-105	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-123	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-125	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-127	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-143	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-145	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-147	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-163	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-165	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-167	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-169	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-171	Vopsit Pulbere	Aluminiu	IP20	30kg	No

Număr de catalog	Finish	Material	Protection Rating	Static Load	Quick Ship
14575-223	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-225	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-243	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-245	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-247	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-265	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-267	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-269	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-271	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-445	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-447	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-463	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-465	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-467	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-469	Vopsit Pulbere	Aluminiu	IP20	30kg	No
14575-471	Vopsit Pulbere	Aluminiu	IP20	30kg	No

DETALII SUPLIMENTARE DESPRE PRODUS

GND / earthing connections in accordance with

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE