

CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



CERTIFICATIONS



CARACTERISTICI

The front panel is bolted to the front frame of the enclosure

SPECIFICAȚII

Material:	Aluminiu
Finish:	Anodized
Accessory Type:	Front panel
Product Type:	Front Panel

Table 1/2

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Front Finish	Rear Finish
30823-209	2U	42HP	3mm	1	Anodized	Anodized
30823-254	3U	28HP	3mm	1	Anodized	Anodized
30823-257	3U	42HP	3mm	1	Anodized	Anodized

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Front Finish	Rear Finish
30823-215	2U	84HP	3mm	1	Anodized	Anodized
30823-269	4U	42HP	3mm	1	Anodized	Anodized
30823-224	3U	63HP	3mm	1	Anodized	Anodized
30823-260	3U	84HP	3mm	1	Anodized	Anodized
30823-227	4U	63HP	3mm	1	Anodized	Anodized
30823-272	4U	84HP	3mm	1	Anodized	Anodized
30823-230	6U	63HP	3mm	1	Anodized	Anodized
30823-284	6U	84HP	3mm	1	Anodized	Anodized

Table 2/2					
Număr de catalog	Treated Edges	EMC Shielding	Height	Width	Quick Ship
30823-209	No	No	84mm	238.7mm	No
30823-254	No	No	128.4mm	167.5mm	No
30823-257	No	No	128.4mm	238.7mm	No
30823-215	No	No	84mm	452.1mm	No
30823-269	No	No	1729mm	238.7mm	No
30823-224	No	No	128.4mm	345.4mm	No
30823-260	No	No	128.4mm	452.1mm	No
30823-227	No	No	172.9mm	345.4mm	No
30823-272	No	No	172.9mm	452.1mm	No

Număr de catalog	Treated Edges	EMC Shielding	Height	Width	Quick Ship
30823-230	No	No	261.8mm	345.4mm	No
30823-284	No	No	261.8mm	452.1mm	No

DETALII SUPLIMENTARE DESPRE PRODUS

Assembly Kit to fix one rear and one front panel is included with the case.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE