


Velcro® Strip 12 x 300 mm

NUMĂR DE CATALOG

20118-624



Velcro® Strip is one of the simplest cable bundling solutions. nVent SCHROFF Velcro® strip allows up to 90 mm diameter of wires.

CERTIFICATIONS



CARACTERISTICI

Length 300 mm (for cable bundles of max. 90 mm diameter)

A = 25 mm, B = 35 mm, C=300 mm, D = 12 mm

ATTRIBUTE PRODUS

Product Type: Hook and Loop Fastener

Type: Cable Tie

Works With: Varistar CP

Material: Polietilenă, Polyamide

Net Weight: 0.025kg

Package Quantity: 10

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O

instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE