

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Rear horizontal rail for backplane mounting with insulation strip



CERTIFICATIONS



CARACTERISTICI

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

SPECIFICAȚII

Material:	Aluminiu
Finish:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/3

Număr de catalog	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-161	3U	175mm	1	Backplane	160mm	Textile
24563-162	3U	235mm	1	Backplane	160mm, 220mm	Textile
24563-163	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Textile
24563-164	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Textile
24563-461	6U	175mm	1	Backplane	160mm	Textile
24563-462	6U	235mm	1	Backplane	160mm, 220mm	Textile
24563-463	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Textile
24563-464	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Textile

Table 2/3

Număr de catalog	Shock and Vibration Tolerance	Handle Included	Mounting	Complies With	Rack Width	Static Load
24563-161	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg
24563-162	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg
24563-163	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg
24563-164	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg
24563-461	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg
24563-462	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg

Număr de catalog	Shock and Vibration Tolerance	HandleIncluded	Mounting	Complies With	Rack Width	Static Load
24563-463	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg
24563-464	5g (force)	No	Rack	IEC 60297-3-103	84HP	15kg

Table 3/3

Număr de catalog	Quick Ship
24563-161	No
24563-162	No
24563-163	No
24563-164	No
24563-461	No
24563-462	No
24563-463	No
24563-464	No

DETALII SUPLIMENTARE DESPRE PRODUS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE