

PSU 19" AC/DC Linear Regulator, Dual

Linear regulator for application which only allows a very low noise level at the outputs.



CERTIFICATIONS



CARACTERISTICI

2 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

SPECIFICAȚII

Table 1/3

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-017	19" Linear Regulator	230V	10W	2	12V	0.4A
13105-018	19" Linear Regulator	230V	12W	2	15V	0.4A
13105-022	19" Linear Regulator	230V	24W	2	12V	1A

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-023	19" Linear Regulator	230V	30W	2	15V	1A
13105-021	19" Linear Regulator	230V	14W	2	5V	1.4A
13105-027	19" Linear Regulator	230V	36W	2	12V	1.5A
13105-028	19" Linear Regulator	230V	45W	2	15V	1.5A
13105-029	19" Linear Regulator	230V	58W	2	24V	1.2A

Table 2/3

Număr de catalog	Voltage 2	Current 2	Rack Height	Rack Width	Depth	Package Quantity
13105-017	12V	0.4A	3U	6HP	171.93mm	1
13105-018	15V	0.4A	3U	6HP	171.93mm	1
13105-022	12V	1A	3U	10HP	171.93mm	1
13105-023	15V	1A	3U	10HP	171.93mm	1
13105-021	5V	1.4A	3U	10HP	171.93mm	1
13105-027	12V	1.5A	3U	14HP	171.93mm	1
13105-028	15V	1.5A	3U	14HP	171.93mm	1
13105-029	24V	1.2A	3U	14HP	171.93mm	1

Table 3/3

Număr de catalog	Certifications	Quick Ship
13105-017	RoHS, CE, EN 62368-1	No
13105-018	CE, EN 62368-1, RoHS	No

Număr de catalog	Certifications	Quick Ship
13105-022	CE, RoHS	No
13105-023	RoHS, CE	No
13105-021	RoHS, CE	No
13105-027	CE, RoHS	No
13105-028	RoHS, CE	No
13105-029	CE, RoHS	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE