

PSU 19" AC/DC Maxpower 100 W, Single, Adjustable



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and a single, adjustable output voltage.

CERTIFICATIONS



CARACTERISTICI

Wide input voltage range 90 ... 264 VAC and 100 ... 360 VDC with active Power Factor Correction (PFC)

1 output voltage

Signalling: Output voltage OK

Wide adjustment range of output voltage

Integrated decoupling diode for redundancy

Active Current Share Bus (CSB)

SPECIFICAȚII

Table 1/2

Număr de catalog	Type	Input Voltage AC	Input Voltage DC	Power	Number of Output Voltages	Voltage 1
13100-134	19" Switched-Mode	90 – 264V		102W	1	16V

Număr de catalog	Type	Input Voltage AC	Input Voltage DC	Power	Number of Output Voltages	Voltage 1
13100-133	19" Switched-Mode	90 – 264V	100 – 360V	100W	1	4.5V

Table 2/2

Număr de catalog	Current 1	Rack Height	Rack Width	Depth	Package Quantity	Quick Ship
13100-134	3.4A	3U	6HP	171.93mm	1	No
13100-133	5.9A	3U	6HP	171.93mm	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order front panel separately.

Output data at mains voltage 190 V AC, Ta= 0 ... 50 °C.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE