

PSU 19" AC/DC Maxpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

CERTIFICATIONS



CARACTERISTICI

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active power factor correction (PFC)

1 output voltage

Signalling: Output voltage OK

High power density

Integrated decoupling diode for redundancy operation

Active Current Share Bus (CSB)

SPECIFICAȚII

Table 1/2

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-105	19" Switched-Mode	90 – 264V	101W	1	24V	4.2A
13100-103	19" Switched-Mode	90 – 264V	100W	1	12V	8.3A

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-104	19" Switched-Mode	90 – 264V	99W	1	15V	6.6A
13100-102	19" Switched-Mode	90 – 264V	80W	1	5V	16A

Table 2/2

Număr de catalog	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-105	3U	6HP	1	No
13100-103	3U	6HP	1	No
13100-104	3U	6HP	1	No
13100-102	3U	6HP	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order front panel separately.

Output data at mains voltage > 190 VAC, $T_a = 0 \dots 50 \text{ }^{\circ}\text{C}$.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE