

PSU 19" AC/DC Maxpower 180 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

CERTIFICATIONS



CARACTERISTICI

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active Power Factor Correction (PFC)

1 output voltage

Signalling: Output voltage OK

Efficiency up to 87 %

Integrated active decoupling for redundancy operation

Active Current Share Bus (CSB)

SPECIFICAȚII

Table 1/2

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-153	19" Switched-Mode	90 – 264V	168W	1	24V	7A
13100-151	19" Switched-Mode	90 – 264V	156W	1	12V	13A

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-152	19" Switched-Mode	90 – 264V	165W	1	15V	11A
13100-150	19" Switched-Mode	90 – 264V	150W	1	5V	30A

Table 2/2

Număr de catalog	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-153	3U	8HP	1	No
13100-151	3U	8HP	1	No
13100-152	3U	8HP	1	No
13100-150	3U	8HP	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order front panel separately.

Output data for mains voltage > 190 VAC, TA = 0 ... 50 °C.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE